

Passive Integrators



Passive integrators are designed to be used with derivative sensors, such as field or current probes, for the measurement of fast pulsed signals. Connected to this type of sensors, the passive integrator produces an overall flat response without the drawbacks of the numerical integration. The output of the passive integrator shall be connected directly to the high impedance input of a fast rise-time measurement device or of a 1 M Ω to 50 Ω impedance matching device.

SPECIFICATIONS



Type	ITR200N	ITR1U2	ITR12U
Time constant	200 ns	1.2 μ s	12 μ s
Cut-off frequency	1.4 GHz	1 GHz	200 MHz
Input impedance	50 Ω		
Peak maximum input	1 kV (100 ns pulse)		
Output loading	>10 k Ω (recommended connection to the oscilloscope's 1 M Ω input)		
Input / output connectors	-A model : N / BNC -S model: SMA / SMA		
Dimensions	-A model (N / BNC) : 63 x 18 x 18 mm -S model (SMA) : 47 x 18 x 18 mm		
Weight	65 g		

Other time constants available on request.

Typical performances

S21 on a 50 Ω load

S21 on a 1 M Ω load



North America Sales, Service & Support



An ISO 9001:2015 registered company

8526 Virginia Meadows Drive
Manassas, VA 20109

Ph: (703) 365-2330

www.hvtechnologies.com

emcsales@hvtechnologies.com

Ordering information

TYPE	DESCRIPTION
ITR200N-A	Passive integrator, T = 200 ns, up to 1.4 GHz, connectors: N(f) - BNC
ITR200N-S	Passive integrator, T = 200 ns, up to 1.4 GHz, SMA(f) – SMA(m)
ITR1U2-A	Passive integrator, T = 1.2 μ s, up to 1 GHz, connectors: N(f) - BNC
ITR1U2-S	Passive integrator, T = 1.2 μ s, up to 1 GHz, SMA(f) – SMA(m)
ITR12U-A	Passive integrator, T = 12 μ s, up to 200 MHz, connectors: N(f) - BNC
ITR12U-S	Passive integrator, T = 12 μ s, up to 200 MHz, SMA(f) – SMA(m)